



# XVLP

TECHNOLOGY BY WAGNER



# WAGNER



## FinishControl 6500 TS

The modular spraying system  
without compromise



Suitable for solvent- and  
waterbased materials.



High operating speed due to  
Visco nozzle and Click & Paint.



Perfectly suitable for small  
and mid-sized projects.

[www.wagner-xvlp.com](http://www.wagner-xvlp.com)

## Direct Spray Control

Work can be easy and convenient. All important device settings can simply be handled at the spray gun. Adapt to the processed material by regulating the infinitely variable air and material flow. The spray pattern and level settings allow to always adapt to the object being sprayed.

## Click and Paint

Switch the material and colour shade in no time at all. Difficult and fiddly replacement of needle valve nozzles is no longer necessary.



## Visco nozzle

The trend-setting slot nozzle has many benefits:

- Better atomisation of high-viscosity coating materials
- High flow rate and fast operating speed
- Perfect surface

## TempSpray


Heating the material allows to spray very high-viscosity lacquers. The TempSpray attachment with integrated stirring device and Teflon® coated container heats up the material. Work at a constant material temperature, no matter what the outside temperature is.

## FinishControl 6500 TS - Scope of delivery



Technical data	FinishControl 6500 TS
Atomisation power	300 Watt
Voltage	230 V / 50 Hz
Max. spray pressure	0.27 bar
Weight	9 kg
Recommended application	Suitable for all lacquers, als for high-viscosity lacquers
Scope of delivery	FinishControl 6500 TS turbine + 5 m air hose with metal handle + Spray attachment „TempSpray“
Article number	2316 089

## Accessories - Spray attachments



### FineSpray (FinishControl 5000 + 6500 TS)

Spray attachment with 1000 ml stainless steel container. Ideally suitable for glazes and low-viscosity materials. (Article number: 2321 877)



### StandardSpray (FinishControl 5000 + 6500 TS)

Spray attachment with slot nozzle and 1000 ml stainless steel container. Compatible with all conventional lacquers. (Article number: 2321 879)



### TempSpray (Only for FinishControl 6500 TS)

Spray attachment with slot nozzle and heated container (600 ml). Heating up the material allows also to spray high-viscosity lacquers. Included as standard with the FinishControl 6500 TS! (Article number: 2321 878)



### WallSpray (FinishControl 5000 + 6500 TS)

Spray attachment with slot nozzle and 1400 ml plastic container. Designed for processing dispersion and latex paints. (Article number: 2321 880)

