# The Quickest and Easiest Way To Prepare Tungsten Electrodes

- Quick & easy setup and operation saves time, eliminates hassles
- Consistently & properly ground electrodes provide optimum, repeatable welding results
- Manufactured in U.S.A. Expert service and spare parts are available immediately
- Proper diamond cutting eliminates risk of electrode splintering & weld rejections

STEP 1 - Diamond Ground Flat





Produces a diamond ground flat surface at the tip of the electrode.





**Ground Flat** 

**STEP 2 - Diamond Ground Taper** 



Produces a longitudinally ground taper with a 20RMS finish and a +/- 1/2° angle tolerance.

# STEP 3 - Diamond Cut-to-Length



Produces smooth diamond cut electrodes on a selectable length scale.



"The Tungsten Electrode Experts"

## DGP-1



- Our most economical grinder
- Accomplishes process steps 1 & 2: Flat and Taper grinding
- For welders who regrind but don't cut, this product provides an all-purpose wheel on the left instead of the cutting apparatus.

#### DGP-2



- A complete system that includes diamond grinding and cutting wheels to accomplish all electrode preparation steps.
- Cutting apparatus includes adjustable stop & scale to allow users to cut as short as .200" (3mm).

#### DGP-3



- A complete system that includes diamond grinding and cutting wheels to accomplish all electrode preparation steps.
- Cutting apparatus includes built-in micrometer indexer for quick and very accurate cuts of different lengths as short as .200" (3mm).

# **ACCESSORIES**

- Vacuum system in insulated cabinet for dust collection
- Short collets for grinding short electrodes
- Flexible spotlight

# **FEATURES**

- No tools required for setup or collet changes
- Flat, grind and cut most electrodes in 60 seconds or less
- Long life, high-quality diamond wheels that are perfect for grinding tungsten
- Fine, longitudinal finish on taper grinding to improve arc stability, starting and consistency
- Taper angle adjustable from 6°-120° with a tolerance of +/- 1°
- Collets available to grind electrodes for .020" to 3/16" (.5mm-4.8mm) diameter

# **APPLICATIONS**

Mechanized / Automatic TIG & Plasma Welding Manual TIG & Plasma Welding Orbital Tube & Pipe Welding

#### **SPECIFICATIONS**

#### **DGP Grinders**

Dimensions: 21.5"(L) x 12"(D) x 12"(H) 564mm x 305mm x 305mm

Weight: 27.2 lbs. / 12.3 kg

Voltage: 115 VAC, 60 Hz, or 220 VAC, 50 Hz option

Amperage: 5.0 Amps

## **DGP Grinders with Vacuum Cabinet**

Dimensions: 26"(L) x 20"(D) x 44"(H) 660mm x 508mm x 1,118mm

Weight: 102 lbs. / 46.4 kg

Voltage: 115 VAC, 60 Hz, or 220 VAC, 50 Hz option

Amperage: 13.5 Amps

#### Piranha II

• Compact/precision tungsten grinder .040"-3/32" (1.0-2.4mm).

# Piranha III

 Heavy duty dedicated tungsten grinder designed for continuous grinding of .040"-3-16" (1.0mm-4.8mm).

#### **Pre Ground Electrodes**

• CNC manufactured high tolerance electrodes for orbital and automatic TIG and plasma welding.

# **Premium Tungsten**

 Thoriated, Lanthanated, Ceriated, Zirconiated, Tri-mix®, Cryo-T®, Pure and specialty materials.



"The Tungsten Electrode Experts"

www.diamondground.com • sales@diamondground.com

US Office: 2651 Lavery Court • Newbury Park, CA 91320 •Tel: 805-498-3837 • Fax: 805-498-9347

European Office: Diamond Ground Products Europe